

Instapak® Quick RT® Packaging

Protective Foam Cushions

Convenient,
Portable, Custom
Protection





157 Green Street ▶ Foxboro, MA 02035
 (508) 543-3800 ▶ Fax (508) 543-0330
 Toll Free (877) 543-4111
 www.accutechpkg.com



Enjoy All Proven Benefits Instapak® Foam Packaging

NO EQUIPMENT NEEDED

Instapak® Quick RT® Foam Packaging is a protective packaging solution you can take and use anywhere.

By expanding up to 27 times their original size, Instapak® Quick RT® foam bags save valuable space, making them the ideal on-demand packaging solution.

For best results, activate bags stored between 65°F to 90°F / 18°C to 32°C.

INSTAPAK® QUICK TUFF® FOAM

Instapak® Quick Tuff® foam provides durable cushioning and blocking and bracing protection for heavy products.

- Easy-to-Use: Anyone can become a packaging expert — instantly.
- Superior Product Protection: Virtually eliminate shipping damage.
- No Start Up Costs: No dispensing system or warming unit required.
- Versatile: Protects products of almost any size, shape and weight.
- Fast: Expands in seconds to form custom-fit protective foam cushions.
- Convenient: Takes up little space and is completely mobile so you can use it anywhere.
- Customer Satisfaction: Product arrives in a neat professional package.

| Quick Tuff® | #25 | #45 | #65 |
|----------------------|-----------------|-----------------|-----------------|
| Flat Bag Size | 18" x 16" | 18" x 20" | 22" x 20" |
| Recommended Box Size | 10" x 10" x 10" | 12" x 12" x 12" | 14" x 14" x 14" |

| Quick RT® | #10 | #20 | #40 | #60* | #80 | #100 |
|----------------------|--------------|-----------------|-----------------|-----------------|-----------------|-----------------|
| Flat Bag Size | 15" x 18" | 18" x 18" | 18" x 24" | 18" x 24" | 22" x 27" | 25" x 27" |
| Recommended Box Size | 8" x 8" x 8" | 10" x 10" x 10" | 12" x 12" x 12" | 14" x 14" x 14" | 18" x 12" x 12" | 16" x 16" x 16" |

*Contains 25% more foam than the #40 bag.

CREATE PROTECTIVE FOAM CUSHIONS IN THREE SIMPLE STEPS

Instapak® Quick RT® protective foam packaging can be activated right out of the box and requires no additional equipment.

See user's guide for complete instructions and helpful hints.



Press

Press firmly on the "A" symbol near the lower left corner of the bag to break the seal.



Pat

Mix the components by firmly patting back and forth 10–20 times on the "A" and "B" symbols.



Pack

Quickly place the expanding bag of foam into the box and nestle the product into the rising foam. Repeat the process as needed.

